

# Industrial Networking IDF

## PROLINE NETWORKING CABINET

nVent HOFFMAN's ProLine Industrial Networking cabinet is designed to house and protect networking equipment and cables that are placed in challenging environments. It comes in a broad range of standard heights, widths and depths. It is fully tested and certified for National and International applications. The cabinet provides easy access to 19-in. rack mounted equipment and cables. ProLine is offered in UL 508A Type 1 and 12 configurations.

The cabinet is offered in painted steel for UL 508A Type 1, 3R, 12 or 4 applications. Rack angles are fully RU marked on all sides and provided with tapped (10-32) or square (.375-in. x .375-in) holes, depending on configuration selected. The rack angles are fully adjustable front to rear in a unitized, easy-to-move fashion.

ProLine Type 1 and 12 cabinets are ideal for securing and protecting rack equipment that is used in applications with wet, hot, and dusty environments.

New models have been introduced that provide provisions for larger AC units – G52 – up to 12,000 BTU cooling capacity.



### KEY FEATURES

- UL 508A Type 1 or 12 offering
- Tool-free hinge pins on doors for easy removal
- Locking door handles
- 19-in. rack angles spaced per EIA standards with RU marked square holes (.375-in. x .375-in.)
- Phosphatized steel coated with polyester paint (Black or Gray)
- Fully accessorized
- Easy access to equipment
- High performance top mounted fan and lower side filters configuration available
- Ready-to-order, AC-ready configuration
  - Precut hole for AC on side of cabinet
  - Order AC separately

### APPLICATIONS INCLUDE:

- Plant floor automation
- Industrial Networking
- Petrochemical and Processing
- Corrosive environments
- Food and Beverage

## SPECIFICATIONS

### FRAME

- Heavy gauge, multi-formed steel

### FRONT / REAR DOOR

- Solid door with vault style 3-point latching and key locking handle
- Window or solid door options

### TOP

- High capacity, sliding gland plate
- Fan ready for extra cooling capacity

### SIDE COVERS

- Modular style makes side covers easy to remove
- AC ready models have precut hole for AC placement order AC unit separately (G28 or G52 depending on selection)

### RACK ANGLES

- 2 sets of EIA universal spaced, field configurable, tapped (10-32) or square hole (.375-in. x .375-in.), depending on configuration. Rack angles are fully adjustable front to rear and RU marked on all sides

### MOBILE BASE WITH CASTERS, LEVELERS, AND CABLE ENTRY GLAND PLATE

- Skirted casters
- Adjustable levelers
- Large gland plate conforms around cables as they enter the cabinet from beneath

### FULL LINE OF EASY-TO-INSTALL ACCESSORIES



Fan and Filter Packages



AC-ready Packages



Order AC unit separately

### North America

Minneapolis, MN  
Tel: +1.763.421.2240  
Mexico City, Mexico  
Tel: +52.55.5280.1449  
Toronto, Canada  
Tel: +1.416.289.2770

### South America

Sao Paulo, Brazil  
Tel: +55.11.5184.2100  
Boituva, Brazil  
Tel: +55.15.3363.9148

### Europe

Betschdorf, France  
Tel: +33.3.88.90.64.90  
Straubenhardt, Germany  
Tel: +49.7082.794.0  
Dzierzoniow, Poland  
Tel: +48.74.64.63.900  
Lainate, Italy  
Tel: +39.02.932.7141

### Middle East & Africa

Dubai, United Arab Emirates  
Tel: +971.4.378.1700  
Bangalore, India  
Tel: +91.80.6715.2001

### Asia

Shanghai, P.R. China  
Tel: +86.21.2412.6943  
Singapore  
Tel: +65.6768.5800  
Shin-Yokohama, Japan  
Tel: +81.45.476.0271  
Seoul, Korea  
Tel: +82.2.2129.7755  
Qingdao  
Tel: +86.532.8771.6101



Our powerful portfolio of brands:

[nVent.com](http://nVent.com)

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER