

RackChiller Rear Door

SMART PRECISION COOLING



nVent SCHROFF RackChiller Rear Door Chilled Water Heat Exchanger is designed for managing high heat load cooling requirements within higher-density server, computing and storage racks. The entire system is integrated within an aesthetically framed perforated door with protective covers to isolate the liquid source and cooling loop from the rack-mounted equipment. The RDC installs on equipment racks as a separate complete rear door, enabling it to be retrofitted to existing racks.

nVent SCHROFF Rear Door Chilled Water Heat Exchanger cools the warm exhaust air generated by the fans in the existing rack-mounted IT equipment through a large cooling coil surface before reintroducing back to the room.


FEATURES

- Passive solution without fans - no noise, no additional power consumption, low maintenance requirements
- Active solution with fans supporting the air flow and minimize pressure drop of the heat exchanger
- Optional water control kit allows water flow regulation according the actual heat load
- Frame solution allows separation of coil and condensate management from the rack mount equipment
- Rear space inside the cabinet is completely available for cabling and power distribution
- Available in 600 mm and 800 mm width in 2,000 mm (42RU), 2,200 mm (47RU) and 2,450 mm (52RU) height
- Easily adapts to nVent cabinets; retrofit kits available for third party cabinets

BENEFITS

- Modular standard design - easy to adapt to your requirements
- Minimal planning outlay, short setup time
- Versatile infrastructure solutions and product combinations





Cooling performance

15kW 35kW 55kW

Parameter		Operating point 1	Operating point 2	Operating point 3
$T_{\text{water, in}}$	[°C]	18	14	10
$T_{\text{water, out}}$	[°C]	22	20	20
$T_{\text{air, in}}$	[°C]	35	45	50
$T_{\text{air, out}}$	[°C]	22	23	25
V'_{air} (projection)	[m ³ /h]	3462	4773	6600
V'_{water} (projection)	[l/min]	60	77	77
Δp_{air}	[Pa]	9	16	28
Δp_{water}	[kPa]	52	84	85

For further information please visit: <https://lp.schroff.nVent.com/en/rackchiller-reardoor>

North America

All locations
Tel: +1.763.422.2661

Europe

Straubenhardt, Germany
Tel: +49.7082.794.0
Betschdorf, France
Tel: +33.3.88.90.64.90
Warsaw, Poland
Tel: +48.22.209.98.35
Assago, Italy
Tel: +39.02.5776151.224

Middle East & India

Dubai, United Arab Emirates
Tel: +971.4.37.81.700
Bangalore, India
Tel: +91.80.6715.2001
Istanbul, Turkey
Tel: +90.216.250.7374

Asia

Shanghai, P.R. China
Tel: +86.21.2412.6943
Singapore
Tel: +65.6768.5800
Shin-Yokohama, Japan
Tel: +81.45.476.0271



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER